

Datasheet

## RS Pro Straight 50Ω Coaxial Adapter BNC Female to BNC Female 4GHz

RS Stock No: **793-3601**



### Product Details

RS Pro straight BNC female to BNC female coaxial adapter comes with waterproof IP68 inner sealing against gas and moisture ingress between insulators, inner and outer conductors and connector body and panel sealing between connector body and panel mounting hole. This waterproof bulkhead jack to jack adapter has a nickel plated brass body, PTFE insulator, silicone gasket and a gold plated centre contact. It is suitable for a variety of applications including video signalling and test equipment.

### Features and Benefits

- BNC female to BNC female coaxial adapter
- Nickel plated brass body, PTFE insulator, silicone gasket and a gold plated centre contact
- 50Ω impedance
- Suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Adapter Type A	BNC
Adapter Type B	BNC
Adapter Type	BNC Socket to BNC Socket
Body Orientation	Straight
Body Plating	Nickel
Contact Material	Brass
Contact Plating	Gold
Gender A	Female
Gender B	Female
Impedance	50 $\Omega$
Length	39.5 mm
Operating Frequency	4 GHz
Body Material	Brass
Insulation Material	PTFE
Operating Temperature	-65 to +165°C
Voltage Rating	500 V