







Hood lower part





Hood upper part



Strain relief 1



Strain relief 2



Flathead screws

				Det.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub hoods 15 poles not shielded	Maßstab/ Scale 1:1
			Detail.	27/02/03	SH			
			Insp.					
			Stand.					
34793	11/01/08	PK	HARTING EURL F-95972 Paris				TB 09 67 015 0571	Blatt/ Page 1 / 1
31392	27/02/03	SH						
Mod.	Det.	Name						
						Sub.		