





## **N** 95 32 060 Cable Cutter

(ratchet action)

with telescopic handles



- Technical details
- Description

<b>No.</b>	95 32 060	
<b>EAN</b>	4003773071563	
<b>Head</b>	burnished	
<b>Handles</b>	with multi-component grips	
	60.00	Ø mm
	740.00	mm <sup>2</sup>
<b>MCM</b>	1400	
	630	mm
	3820	g

- for copper and aluminium cables, single and multiple wire - also with hard rubber or plastic sheath
- not suitable for steel wire and wire ropes
- also suitable for cables with iron sheath reinforcement
- little handforce required for cutting due to optimum transmission ratio
- high cutting capacity due to two-hand operation and ratchet action
- the blade can be opened in any cutting position
- handle length with multiple position adjustment from 400 - 600 mm (short transport length, individual adaptation to working conditions)
- Blade: special-quality high-grade tool steel, oil-hardened
- handles: high-strength oval aluminium tubing

**Spare Parts**

<b>No.</b>	<b>EAN</b>	
95 39 720	4003773025290	Movable spare blade for 95 31 720 / 95 32 060

technical change and errors excepted