

## Prohibition sign - PML-P102 (D200) - 1014189

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Prohibition sign, Sheet, red/white, labeled: Do not connect, Mounting type: Adhesive, Diameter: 200 mm, Lettering field: d: 200 mm

### Why buy this product

- Stick-on prohibition signs, preprinted with symbol
- Suitable for indoor and outdoor use
- The prohibition signs conform to the ISO 7010 international standard



### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 046356 784849
Weight per Piece (excluding packing)	20.29 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width (a)	200 mm
Diameter	200.00 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

#### General

Color	red/white
Type	Round
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

## Prohibition sign - PML-P102 (D200) - 1014189

### Technical data

#### General

Printing	Do not connect
Number of individual labels	1
Marking mounting type	Adhesive

### Classifications

#### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27141137

#### ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777

#### UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107