


TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



PORTABLE TOOLS TRANSFORMER

TYPE: ISOLATION

INPUT: 240V 50Hz

OUTPUT: 55-0-55V

RATING: 1.5KVA INTERMITTENT
5MINS ON 15MINS OFF

THERMAL CUT-OUT: 6A

OUTPUT SOCKET: 2x16A BS EN 60309

INPUT PLUG: 13A BS1363

ENCLOSURE: GRP

COLOUR: YELLOW

REV	4	CARROLL & MEYNELL TRANSFORMERS LIMITED TEL: 01642 617406 FAX: 01642 614178 enquiries@carroll-meynell.com	TITLE	PORTABLE TOOL TRANSFORMER CM15002	DRAWN	PROJECTION	DATE	SCALE	
	3		SH			26/4/8	NTS		
	2		ALL DIMENSIONS IN mm			DRAW No	3256	REV	PAGE
	1							0	1/1