

Datasheet

RS Pro NPIS104F Series Shielded Wire-wound SMD Inductor 22 μ H \pm 20% 2.5A Idc

RS Stock No: 741-9293



Product Details

RS Pro shielded wire-wound SMD inductor offers inductance of 22 μ H and withstands DC current up to 2.5 A. This shielded inductor works with DC-DC converters.

Features and Benefits

- Magnetically shielded which results in a low leakage field
- High saturation current
- High reflow temperature compatible
- Suitable applications DC/DC convertors

**Specifications:**

Inductor Construction	Wire Wound
Shielded	Yes
Depth	10.5 mm
Dimensions	10.6 x 10.5 x 4 mm
Height	4 mm
Length	10.6 mm
Maximum DC Current	2.5 A
Maximum DC Resistance	73 mΩ
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-25°C
Tolerance	±20%
Inductance	22 μH
Package/Case	104
Package Type	Tape & Reel