

Datasheet

Rigid Conductive Box with Insert

RS-217-9883



Top



Bottom

Description:

RS Rigid Conductive Boxes are marked with the ESD protective symbol. The Boxes have the RS logo and part number applied to the bottom. They meet EN 61340-5-1 and Packaging standard IEC 61340-5-3.

Properties:

Size:	35mm x 35mm x 11mm
Insert Size:	28mm x 28mm
Material:	Black conductive polypropylene
Resistance (Rs):	$< 1 \times 10^5$ ohms (per IEC 61340-2-3)
Size Tolerance:	± 0.8 mm
Melting Temperature:	80°C to 90°C
Hinge:	Moulded one-piece
Closure:	Snap
Top Foam:	6mm thick low density foam (FX)

All boxes have the ESD Protective Symbol moulded into them.



"Packaging, when required, shall be defined for all material movement within protected areas, between protected areas, between job sites, field service operations and to the customer." [IEC 61340-5-1 clause 5.3.4 Packaging]

Unless otherwise noted, tolerance $\pm 10\%$

Specifications and procedures subject to change without notice.