



**ACCURATUS®**  
BY CERATECH

### **Mini QWERTY POS Keyboard**



**Model Number: KYB500-S69A**

#### **Key Features:**

- Compact keyboard with QWERTY section, with programmable keys
- High quality membrane keys with tactile feeling
- Laser-engraved keycap symbols or high quality UV silk screen printed keycap symbols
- Damaged keys can be easily replaced and hence save the replacement cost
- With internal strong metal plate to enhance the protection against ESD is increased
- Different relegendable keycaps (1-fold, 2 fold) are available

#### **Key Lock Features:**

- 6 steps Keylock
- Life cycles: > 25,000
- Have tactile feeling

#### **Magnetic Stripe Reader Features:**

- Comply with ISO 7812, IBM standards, American Driving License
- Support multi-country code settings
- Support programmable MSR setting for the header, tailor, separator, suffix and prefix, track sequence
- Track 1: 210BPI with max 76 characters
- Track 2: 210BPI with max 107 characters or 75BPI with max 37 characters
- Track 3: 210BPI with max 107 characters
- Card swipe speed: 10 to 100 cm/s
- 500,000 swipe cycles
- Available Configuration
  - Dual Track: Track 1 & 2 or Track 2 & 3
  - Three Track: Track 1, 2 & 3



#### **Dimensions:**

335(L) \* 170(W) \* 47(H) mm

#### **Programmable Features:**

- All keys can be programmed with unlimited characters
- All data can be retained for no less than 100 years without additional battery
- Does not require a TSR program and hence avoids application software crashes
- Provides multi-level programming
- Provides for a variable time delay of up to 255 seconds in each programmed string
- Provides true keyboard wedge function that operates with or without the normal computer keyboard connected
- Provide a true Caps/Scroll/Numeric Lock function independent of any other keyboards being connected
- Support PS/2 programming in DOS, Windows9X, Me, 2K, XP