

LOC GP	DIST 00	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
					A	REVISED PER EC 0513-0160-03	22MAY03	JG

CABLE SUPPLIED
BY CUSTOMER



STRAIN RELIEF STAPLE (1 SUPPLIED)
MATERIAL: STEEL
FINISH: SEE TABLE

SPRING LATCH (2 SUPPLIED)
MATERIAL: STAINLESS STEEL

MACHINE SCREW (2 SUPPLIED)
#2-56 UNC X.250

CONNECTOR (MUST BE
PURCHASED SEPARATELY)

32.77
[1.290]

33.91
[1.335]

UPPER BACKSHELL (1 SUPPLIED)
MATERIAL: ZINC
PLATING: NICKEL OVER COPPER

10.16
[.400]

LOWER BACKSHELL (1 SUPPLIED)
MATERIAL: ZINC
PLATING: NICKEL OVER COPPER

1 .270 MAX CABLE DIA

2. DIMENSIONS IN BRACKETS ARE IN INCHES.

3 BRIGHT TIN-LEAD OVER NICKEL.

4 BRIGHT TIN OVER NICKEL.

METRIC

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES- MM
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± 0.38 [.015]
ANGLES ± -

MATERIAL

-

FINISH

-

DR 05/08/89
M.MCCAFFREY
CHK 05/11/89
M.E.SHIRK
APPD 05/23/89
J.BROSHARD

APPD -

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT -

4	749608-2
3	749608-1
STAPLE FINISH	PART NO

AMP

AMP INCORPORATED
Harrisburg, Pa. 17105

NAME
INDIVIDUAL KIT, 26 POSITION,
REDUCED WIDTH, STRAIGHT EXIT,
UNKEYED, AMPLIMITE .050 Series

SIZE	FSCM NO	DRAWING NO
B	00779	749608
SCALE	SHEET	
2:1	1 OF 1	