

## Non sparking hammer 487

Finish: polished  
Material: ALUMINIUM-BRONZE  
Non-sparking and anti-magnetic  
Standard No: II B



|                 |  |               |   | A<br>mm | B<br>mm | C<br>mm |      |      |
|-----------------|--|---------------|---|---------|---------|---------|------|------|
| <b>487-650</b>  |  | 7314150133116 | 1 | 93      | 310     | 30      | 450  | 610  |
| <b>487-1300</b> |  | 7314150133123 | 1 | 112     | 400     | 40      | 1000 | 1300 |
| <b>487-1800</b> |  | 7314150133130 | 1 | 132     | 400     | 44      | 1500 | 1800 |
| <b>487-2300</b> |  | 7314150133147 | 1 | 137     | 400     | 50      | 2000 | 2300 |
| <b>487-5200</b> |  | 7314150133154 | 1 | 176     | 900     | 63      | 4000 | 4900 |
| <b>487-5900</b> |  | 7314150133161 | 1 | 189     | 900     | 66      | 5000 | 5900 |

