



Product Datasheet

ENGLISH

RS Clear Unreinforced PVC Hose



RS Clear PVC Hose

A versatile, clear PVC tubing with a smooth bore suitable for a wide range of low pressure applications.

Tough, flexible and durable under normal operating conditions and able to maintain flexibility even in cold weather conditions.

Technical data

- Medium soft flexible PVC crystal compound
- Temp Range -10°C to +55°C
- Hardness Shore A15
- Tensile strength 10.1 MPa
- F & DA listed ingredients
- Relative Density 1.222gm/cm³



ENGLISH

RS Stock Number	I.D mm	O.D mm	Wall Thickness mm	Min Bend Radius mm
7989985	3	6	1.5	24
7989994	5	8	1.5	40
7990004	6	9	1.5	48
7989997	8	11	1.5	64
7990008	10	13	1.5	80
7989991	12	15	1.5	96
7990017	25	31	3	200
7990001	32	41	6	256