




LOC	DIST	REVISIONS					
FT	8	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AC	REVISED PER ECO-07-025670	11/5/07	SS	GS
			AC1	REVISED PER ECO-09-021826	11JAN10	KK	AEG



- ① PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- ② DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, BLUE.
- ③ AMP PART NO THIS AREA. DATE CODE AT AMP'S OPTION.
- ④ MARK KS 21303, L10.
5. WHEN MATING WITH BLOCK 201357, ACCOMODATES TYPE II, TYPE III+ OR TYPE VI #16 PIN OR SOCKET CONTACTS.
- ⑥ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	43.08 [1.696]	3.86 [.152]	 		200838-9
		43.08 [1.696]	3.86 [.152]			200838-3
		42.82 [1.686]	3.99 [.157]			200838-2
		Z	Y	MARKING	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. REIFSNYDER 07 DEC 95		Tyco Electronics Corporation	
		CHK R. STONE 29 FEB 96		Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD G. STEINHAUER 20 MAR 96		BLOCK, FEMALE, 34 PLACE MINIATURE RECTANGULAR, M SERIES	
		PRODUCT SPEC			
		—			
		APPLICATION SPEC			
MATERIAL		FINISH		SIZE	CAGE CODE
SEE TABLE		—		DRAWING NO	
				RESTRICTED TO	
				—	
		CUSTOMER DRAWING		SCALE 3:1	
				SHEET 1 of 1	
				REV AC1	