







LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
J	—	P4		ADDED 3-5175444-1	ECR-10-008921	26APR10	TS	KB



- NOTES; Δ MUST BE KEPT BETWEEN $-Z$ AND 2
2 THE MATING PLUG HSG. PART NUMBER; 174515, 175442
3 RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH MAX. >
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 0.4N-m (4Kg-cm) MAX.)
4 APPLICABLE PRODUCT SPEC NO. 108-5280
 Δ CIRCUIT NUMBER
POWER CIRCUIT NO. ① ~ ⑱
SIGNAL CIRCUIT NO. ⑲ ~ ⑳
 Δ INDICATED PREFIX AND ID MARK OF PRODUCT P/N BY HOT MARK

注記

- Δ $-Z$ 面から2mmの範囲で測定
2. 嵌合相手ハウジング型 174515, 175442
3. 推奨取付ねじ: JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク: 0.4N-m (4Kg-cm) 以下)
4. 適用製品規格番号: 108-5280
 Δ 回路番号
パワー回路 ① ~ ⑱
シグナル回路 ⑲ ~ ⑳
 Δ 適用製品型番のプリフィックス及びIDマークを
カラーホットマークにて表示



54	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8		-	20, 24, 26~28, 32~34	GRAY	4-5175444-6	
53	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT) × 26		-	-	-	-	
		SELECTIVE GOLD × 13		2~5	20~24, 29~32	WHITE	3-5175444-1	
		SELECTIVE-TIN (BRIGHT) × 21		-	-	-	-	
SEE CUSTOMER DRAWING 9-175444-1								9-175444-1
7	TIN-LEAD	SELECTIVE GOLD × 8		14, 17, 18	24~26, 32, 34	GRAY	7-175444-6	
6	TIN-LEAD	PRE-TIN × 26		-	19~22, 27~30	WHITE	6-175444-1	
		SELECTIVE GOLD × 8		-	-	-	-	
5	TIN-LEAD	PRE-TIN × 26		4, 6, 9, 12	26, 28, 29, 34	LIGHT GRAY	5-175444-9	
		SELECTIVE GOLD × 8		-	-	-	-	
5	TIN-LEAD	PRE-TIN × 30		5, 6, 11, 12	-	GRAY	5-175444-6	
		SELECTIVE GOLD × 4		-	-	-	-	
5	TIN-LEAD	PRE-TIN × 30		4, 6, 9, 12	26, 28, 29, 34	BLACK	5-175444-2	
		SELECTIVE GOLD × 8		-	-	-	-	
5	TIN-LEAD	PRE-TIN × 26		4, 6, 9, 12	26, 28, 29, 34	WHITE	5-175444-1	
		SELECTIVE GOLD × 8		-	-	-	-	
4	TIN-LEAD	PRE-TIN × 26		-	20, 24, 26~28, 32~34	GRAY	4-175444-6	
		SELECTIVE GOLD × 8		-	-	-	-	
3	TIN-LEAD	PRE-TIN × 26		2~5	20~24, 29~32	GRAY	3-175444-6	
		SELECTIVE GOLD × 13		-	-	-	-	
3	TIN-LEAD	PRE-TIN × 21		2~5	20~24, 29~32	BLACK	3-175444-2	
		SELECTIVE GOLD × 13		-	-	-	-	
3	TIN-LEAD	PRE-TIN × 21		2~5	20~24, 29~32	WHITE	3-175444-1	
		SELECTIVE GOLD × 13		-	-	-	-	
2	TIN-LEAD	PRE-TIN × 21		-	19~34	WHITE	2-175444-1	
		SELECTIVE GOLD × 16		-	-	-	-	
0		PRE-TIN × 18		-	-	ORANGE	175444-8	
0		PRE-TIN × 34		-	-	GRAY	175444-6	
0		PRE-TIN × 34		-	-	BLUE	175444-5	
0		PRE-TIN × 34		-	-	-	-	
8	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT) × 34		-	-	WHITE	175444-3	
0		PRE-TIN × 34		-	-	BLACK	175444-2	
0		PRE-TIN × 34		-	-	WHITE	175444-1	
△ MARKING マーキング	SOLDERING SIDE 手付け側	CONTACT SIDE 接触部側	POWER CIRCUIT NO. パワー回路番号	SIGNAL CIRCUIT NO. シグナル回路	COLOR 色	PART NUMBER 製品型番		
	CONTACT FINISH コネクタ仕上	△	GOLD PLATED CIRCUIT NO. 金めっき回路番号					

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN M.KADOSAKI	120CT05	Tyco Electronics Corporation Kawasaki, Japan	
				CHK T.SHINOHARA	120CT05		
				APVD K.BESTUI	120CT05	34POSITION CAP HOUSING ASS'Y 040/070 SERIES HYBRID I/O CONNECTOR	
				PRODUCT SPEC 製品規格			
				APPLICATION SPEC 取付適用規格		SIZE A2	
				WEIGHT			
				CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO C=175444
						SCALE 尺度 2:1	SHEET 1 of 1
						REV P4	