

Cable gland - VC-EMV-KV-PG21(11,5-15,5/13,5) - 1854242

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PG21 EMC half screw connection, for size 2 - 4 metal housing, comprising rubber seal, iris spring, cone discs, and pressure screw, for size 1 housing, cable shielding clamping area: 9.5 - 13.5 [mm], cable: 11.5 - 15.5 [mm]



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 145828
Weight per Piece (excluding packing)	47.8 g
Custom tariff number	85369010
Country of origin	Poland

Technical data

Dimensions

Wrench size, union nut	30 mm
External cable diameter	11.5 mm ... 15.5 mm
Shield diameter	13.5 mm

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Material, pressure screw	Nickel-plated brass
Seal material	TPE
Shielded	Yes
Thread type on seal side	Pg21
Tightening torque, union nut	10.00 Nm

Cable gland - VC-EMV-KV-PG21(11,5-15,5/13,5) - 1854242

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
