



ENGLISH

Datasheet Stock

No: 535-985

RS Pro 3 Core Unscreened Black 3183Y Mains Power Cable

FLEXIBLE - 300/500 V

H05 VV-F

NF C 32-201 - HD 21.5 - CEI 227-5

CONDUCTOR

Metal : Plain copper wire - flexible class 5.

Max operating temperature : 60°C. Max short circuit temperature : 150 °C.

INSULATION

PVC. Identification colors of sheathed cable cores

H05 VV-F	brown-blue	brown-blue-G/Y	black-grey-brown-G/Y	grey-blue-brown-black-G/Y



OUTER SHEATH

PVC. Colors : grey, white or black. **Printing** : < HAR > H05 VV-F

USE

Cables suitable for home and office contesits / Suitable for domestic appliances. Suitable for cooking and heating appliance.

Recommended mini bending radius : 6 D.

+5°C +60°C	Mediocre	Acceptable	Good	Good	Excellent	Acceptable

SIZE MM ²	APPROX OVERALL DIAMETER MM	APPROX WEIGHT KG/KM
2 CORES		
0,75	7,2	55
1	7,5	63
1,5	8,6	82
2,5	10,6	126
4*	12,1	173
3 CORES		
0,75	7,6	65
1	8	76
1,5	9,4	104
2,5	11,4	160
4*	13,1	220
4 CORES		
0,75	8,3	78
1	9	96
1,5	10,5	130
2,5	12,5	194
4*	14,3	270
5 CORES		
0,75	9,3	97
1	9,8	115
1,5	11,6	160
2,5	13,9	238
4*	16,1	350

* Non HAR