

Datasheet

Anti Surge T HBC min fuse, 10A 6.35 x 32mm

RS Stock number [414-061](#)



Description:

Ceramic Body - (T) HBC

All fuses 6.3mm (0.25in) diameter and 32mm (1.25in) in length.

Professionally Approved Products, gives you professional quality parts across all product categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

Anti Surge HBC/LBC (Cartridge Fuses)

Specification:

- Body Material: Ceramic
- Breaking Capacity at Maximum Voltage Rating: 1500 A
- Current Rating: 10A
- Diameter: 6.35mm
- Fuse Speed: T
- Height: 32mm
- High Rupture Capacity: Yes
- Voltage Rating: 500 V ac