

电缆插头外壳 - KGG-MSTB 2,5/ 3 - 1803947

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



电缆插头外壳，针距: 0 mm，位数: 3，尺寸a: 15 mm，颜色: 绿色

RoHS

关键商业数据

包装单位	10 STK
最小订货量	10 STK
GTIN	 4 017918 046095
GTIN	4017918046095
海关税则号	8536901900
Sales Key	AAAFIA

技术数据

尺寸

间距	0.00 mm
尺寸a	15 mm

概述

产品范围	KGG-MSTB 2,5
位数	3
绝缘材料组	I
绝缘材料	ABS
阻燃等级，符合UL 94	HB

标准和规范

阻燃等级，符合UL 94	HB
--------------	----

Environmental Product Compliance

China RoHS	环保使用期限：无限期 = EFUP-e
	无超标的有害物质

电缆插头外壳 - KGG-MSTB 2,5/ 3 - 1803947

分类

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000879
ETIM 5.0	EC000437
ETIM 6.0	EC000437

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	31261501

认证

认证

认证

EAC

防爆认证

认证详情

EAC		B.01742
-----	---	---------

附件

附件

端子标识

电缆插头外壳 - KGG-MSTB 2,5/ 3 - 1803947

附件

用于端子的标记条 - SBS 2,5/7,5 - 1007604



用于端子的标记条，卡，白色，未标记，适用的打印机：CMS-P1-PLOTTER，打孔，安装方式: 卡接到高型标记槽，卡接到扁平式标记槽，适用的模块宽度：7.5 mm，标识区域大小: 15 x 7.5 mm