

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		K	SR10-0457-02	24-10-02	KV	—
			L	ECR-07-008767	16-07-07	BSV	KMA
			M	ECR-09-004273	02-03-09	AEG	KMA

- NOTES:
- 1

THIS RECEPTACLE ACCEPTS SIZE 20 REC. CONTACTS.
- 2

MAXIMUM WIRE INSULATION RECOMMENDED FOR USE WITH THIS RECEPTACLE IS 1,73 DIA. MAX..
- 3

RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- 4


FOLLOWING INSERTION/REMOVAL TOOLS ARE RECOMMENDED FOR USE WITH THESE CONNECTORS:
32-28AWG/28-24AWG CONTACTS
91067-3 INSERTION/REMOVAL
726363-1 INSERTION ONLY
24-20AWG CONTACTS
726363-1 INSERTION ONLY
726364-1 REMOVAL ONLY
- 5

INSERTS: GLASSFILLED SELF-EXTINGUISHING PBT, COLOR BLACK.
- 6


TE, PARTNUMBER AND DATE CODE; INK STAMPED.
- 7

RAISED CAVITY IDENTIFICATION 0,8 HIGH.
- 8

RAISED CAVITY IDENTIFICATION NUMBERS ON WIRE SIDE ARE WHITENED FOR 164534-9.



OBSOLETE	BRIGHT TIN	BRIGHT TIN	STEEL	164534-9	8
	BRIGHT TIN	BRIGHT TIN	STEEL	164534-4	
	PLATING FRONT SHELL	PLATING REAR SHELL	MATERIAL SHELLS	PARTNUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.KESSLER 11FEB99	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK W.SOOMERS	NAME 37 POS HDP-20 RECEPTACLE CONNECTOR SIZE 4 —					
		APVD W.SOOMERS						
	0 PLC ± —	PRODUCT SPEC —						
	1 PLC ± —	APPLICATION SPEC —						
	2 PLC ± —	—						
	3 PLC ± —	—						
	4 PLC ± —	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL —	FINISH —	WEIGHT —	A3	—	C- 164534	—		
CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV	M