



ENGLISH

Datasheet

Straight Die Grinder

6mm Air Powered Mini Angle Die Grinder

[RS Stock No. 739-8452](#)



Specifications:

Power source	: Compressed air
Maximum permissible operating pressure	: 90 psi (6.2 bar)
Recommended operating pressure	: 90 psi (6.2 bar)
Size	: 6mm
Collet Free Speed	: 19,000RPM
Weight	: 0.34kgs / 0.75lbs
Length	: 4.33" / 110mm
Min Hose Size	: 3/16"
Air inlet thread	: 1/4"
Sound	: 82dBA
Vibration	: 4m/s ²
Ave Air Consumption	: 1.68cfm / 47.6 l/min
Recommended lubrications	: 10 Weight SAE Oil

Features:

- Angle head allows the operator to inspect work area more closely
- Compact and lightweight design allows maximum operator control and performance
- Rear exhaust to keep airflow away from work area
- High power motor for consistent performance