

Product Name	FI-W31P-HFE
Series Name	FI Series
Contact spacing (mm)	1.25
Number of rows	2
Number of Contacts	31
Lead free	Yes
Connector type	Board side Receptacle
PCB mounting type	Standard type
PCB mounting method	Solder (SMT)
Wire termination method	-
Applicable wire	-
Finish of contact in connecting area	Gold over Nickel
Finish of contact in terminal area	-
Finish of contact in PCB mounting area	Tin/Tin-alloy over Nickel
Material of housing	Glass-filled PPS (UL94V-0)
PCB side connector styles	Right angle
PCB mounted height (mm)	3.7
Electro magnetic shield function	No