

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [121208-0083](#)
Status: **Active**
Overview: Brad® mPm® DIN Valve Connectors
Description: mPm® DIN Valve Connector, Form B - Industrial, External Thread, 2 Pole Plus Ground with C4 Circuit, 230V, Amber LED, Transparent Nitrile Gasket

Documents:

[Drawing \(PDF\)](#) [Test Summary STR-1251 \(PDF\)](#)
[Product Specification PS-121201-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	121208
Form	B - Industrial
IP Rating	IP65, IP67
Overview	Brad® mPm® DIN Valve Connectors
Product Name	mPm®
Type	Field Attachable Connector
UPC	884982510012

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	19.489/g
Orientation	90° Angle
Pitch - Mating Interface	11.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16A
Voltage - Maximum	230V

Material Info

Old Part Number	S22200TC4M0R
-----------------	--------------

Reference - Drawing Numbers

Product Specification	PS-121201-001
Sales Drawing	SD-121208-001
Test Summary	STR-1251



EU RoHS

RoHS Compliant by Exemption
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[121208Series](#)