




NOTES:

1. MATERIAL



- 1.1 HDMI CABLE: (7/0.10TC*1P+7/0.10TC+FAM)*4PCS+7/0.12TC*3C+7/0.12TC*1P+AL+7/0.12TC+128/0.12ALM+BLACK PVC JACKET.
OD: $\varnothing 6.0 \pm 0.2 \text{ mm}$
- 1.2 HDMI 19PIN TYPE A MALE : BLACK INSULATION, GOLD PLATED CONTACTS, NICKEL PLATED SHELL.
- 1.3 DVI(18+1) MALE: BLACK INSULATION, GOLD PLATED CONTACTS G/F, NICKEL PLATED SHELL.
- 1.4 THUMB SCREW TO BE MOLDED BLACK PVC. NICKEL PLATED SCREW.
- 1.5 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
- 2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
- 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
- 2.4 HI-POT: DC300V/0.01S.

3. PACKAGING: A PC/PE-BAG PACKAGING .

4. ALL MATERIALS ARE REACH COMPLIANT.



PIN OUT


P1	P2	
1	2	BLUE
3	1	WHITE
2	3	DRAIN
4	10	BLUE
6	9	WHITE
5	11	DRAIN
7	18	BLUE
9	17	WHITE
8	19	DRAIN
10	23	BLUE
12	24	WHITE
11	22	DRAIN
15	6	RED
16	7	WHITE
17	15	YELLOW
18	14	ORANGE
19	16	PURPLE
SHELL	DRAIN	SHELL

P/N	L(mm)
11.99.5519	1000±30mm
11.99.5522	2000±50mm
11.99.5532	3000±70mm
11.99.5552	5000±70mm



02	ADD THE ONE	2012-01-05
01	CHANGE THE CABLE MARKING	2011-02-23
00	NEW ISSUE	2010-03-16
REV.	MODIFY DESCRIPTION	DATE

LENGTH TOLERANCE:	SCALE:
X. ± 0.5	FREE
.X ± 0.2	UNIT:
.XX ± 0.1	mm
ANGLE TOLERANCE:	VERSION:
X' $\pm 3^\circ$	02
.X' $\pm 1^\circ$	



VALUE DVI Cable, DVI M-HDMI M, black

ENG:

CHECKED:

APPROVED: