

PICCOLO PC B 65 T



Sample photo

Order symbol: PC B 65 T
Product nbr: 8724003
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074001948
EI. number:
 Finland: 3423501
 Electric No. 8212001488
 Denmark:
 Electric No. Italy: 7202010
 Electric No. Sweden: 2536832

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	110	80	65	B-3 FP 22040
inch:	4.3	3.1	2.6	DIN-35 Mounting rail Wall fastening lug (2 pcs)

Materials:	Rating:
Material: Polycarbonate	Ingress Protection (EN 60529): IP66/67
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: Clear transparent	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	UV resistance: UL 508
Gasket material: Polyurethane	Flammability Rating: UL 746C 5V
	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13

Temperatures:	Certificates:
Temperature °C (short term): -40 ... 120 °C	Germanischer Lloyd (GL)
Temperature °C (continuous): -40 ... 80 °C	SGS Fimko
Temperature °F (short term): -40 ... 250 °F	Gost R
Temperature °F (continuous): -40 ... 175 °F	

Accessories:
B-MP Mounting plate

