




注記
NOTES:
I. 嵌合相手: 5264 シリーズ
MATES WITH: 5264 SERIES.

ウエハー: 66ナイロン。ガラス入り。UL 94V-0
WAFER: 66NYLON, GLASS REINFORCED, UL 94V-0



39.9	38.5	35	22-03-5155	5267-15A	15
37.4	36	32.5	-5145	-14A	14
34.9	33.5	30	-5135	-13A	13
32.4	31	27.5	-5125	-12A	12
29.9	28.5	25	-5115	-11A	11
27.4	26	22.5	-5105	-10A	10
24.9	23.5	20	-5095	-09A	9
22.4	21	17.5	-5085	-08A	8
19.9	18.5	15	-5075	-07A	7
17.4	16	12.5	-5065	-06A	6
14.9	13.5	10	-5055	-05A	5
12.4	11	7.5	-5045	-04A	4
9.9	8.5	5	-5035	-03A	3
7.4	6	2.5	22-03-5025	5267-02A	2
C	B	A	EDP NO.	ENG. NO.	極数 NO OF CKT.

材料 MATERIAL			MOLLEX JAPAN CO., LTD. 日本モレックス株式会社		
仕上げ FINISH			REVISE ONLY ON CAD SYSTEM		
適用電線範囲 WIRE RANGE			TITLE 名称		
被覆外径 INS. RANGE			2.5 LOW PROFILE WAFER ASS'Y		
DRAWN BY 6/20/88 Y. MIZUNO			CHK'D BY '96/03/26 Y. MIZUNO		
APP'D BY '96/03/26 M. FUKUSHIMA			尺度 SCALE 5:1		
記号 LTR			DWG. NO. SD-5267-NA		
変更内容 REVISION RECORD			REV B		
DR. CHK. DATE					