


## Electronic housing - EMG 15-H 7,5MM KLAR - 2947828

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design.  
Height: 7.5 mm, width: 15 mm



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 082932
Weight per Piece (excluding packing)	1.25 g
Custom tariff number	85472000
Country of origin	Germany

### Technical data

#### General

Housing type	Component housing
Housing material	Polycarbonate, PC
Color	transparent

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Dimensions

Length	38 mm
Constructional height	7.5 mm
Width	15 mm

#### Technical data

Inflammability class according to UL 94	V2
Number of positions	6

### Classifications

#### eCl@ss

eCl@ss 4.0	27180401
------------	----------

## Electronic housing - EMG 15-H 7,5MM KLAR - 2947828

### Classifications

#### eCl@ss

eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

#### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501