

MATERIALS AND FINISH

BODY: ZINC ALLOY
PLATED TIN OVER NICKEL OVER COPPER


CENTER CONTACT: PHOSPHOR BRONZE
PLATED SEE TABLE

INSULATOR: TEFLON


LOW PROFILE JAM NUT, HEX HEAD NUT: BRASS
PLATED NICKEL

WASHER: PHOSPHOR BRONZE
PLATED NICKEL


ALL PARTS PACKAGED IN TRAYS
EXCEPT AS NOTED



RECOMMENDED PCB
HOLE PATTERN







LOW PROFILE JAM NUT
2.50/.098 WIDTH



RECOMMENDED PANEL CUTOUT
MAX PANEL THICKNESS: SEE TABLE

BNC JACK
INTERFACE



73171-3357	10u GOLD CONTACT/ HARDWARE NOT INCLUDED	2.00/.079 MAX
73171-3356	73171-3350 PACKED ONE PER BAG	2.00/.079 MAX
73171-3355	30u GOLD CONTACT/ HARDWARE NOT INCLUDED	1.52/.060 MAX
73171-3354	10u GOLD CONTACT/ HARDWARE INCL'D: LOW PROFILE JAM NUT & WASHER	1.52/.060 MAX
73171-3353	30u GOLD CONTACT/ HARDWARE INCLUDED: WASHER AND HEX HEAD NUT	1.52/.060 MAX
73171-3352	10u GOLD CONTACT/ HARDWARE INCLUDED: WASHER AND HEX HEAD NUT	1.52/.060 MAX
73171-3351	30u GOLD CONTACT/ HARDWARE INCLUDED: LOW PROFILE JAM NUT ONLY	2.00/.079 MAX
73171-3350	10u GOLD CONTACT/ HARDWARE INCLUDED: LOW PROFILE JAM NUT ONLY	2.00/.079 MAX
PART NO.	DESCRIPTION:	PANEL THK

PS-89675-2020		ELECTRICA/MECHANICAL	
SPECIFICATION		DESCRIPTION	

CHG: ADDED - 3357 PER PDR1106824 EC NO: URF2012-0089 DRWN:WE102 2011/06/29 CHKD: APPR:MHUANG 2011/08/25	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY JDW		DATE 2008/01/17		TITLE BNC JACK RA PCB 75 OHM 3 GHZ BULKHEAD RM EWR 3520 BNC-J/PCB			
			4 PLACES	± ---	± ---	CHECKED BY SSS		DATE 2008/01/17					
			3 PLACES	± ---	± ---	APPROVED BY JWIENER		DATE 2010/02/03		MOLEX INCORPORATED			
			2 PLACES	± ---	± ---	MATERIAL NO.		DOCUMENT NO.					
1 PLACE	± ---	± ---	ANGULAR ± 2 °		SEE TABLE		SD-73171-335		1 OF 1				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										