

Datasheet

Art.No. 92.040.1053.1

Distributor GST18i4V 2P1T V SW

T-connector GST18i4, 4 pole, 1 input, 2 outputs, 250/400 V, 20 A, colour of coding: black



Art.No.	92.040.1053.1
EAN	4015573655898
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

Model

Number of poles	4
Number of inputs	1
Number of outputs	2
Type of fastening	No
Degree of protection (IP)	IP20
Type of distributor	T-distributor

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	44 mm
Width	38 mm
Height	43 mm

Accessories

Art.No.:	Type:	Description
05.564.5353.0	Cover cap GST18i3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	Cover cap GST18i3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9153.0	Cover cap GST18i4 SOCKETS	Cover for female connectors GST18i4, black
05.588.5753.0	Locking slide GST18 WS	Locking device for distributor GST18i3-5, retrofit part, white
05.588.5753.1	Locking slide GST18 SW	Locking device for distributor GST18i3-5, retrofit part, black

