

Datasheet

Stock No: 810-7323

RS Pro 2 Core Unscreened Grey 2192Y Power Cable



STANDART	:	CENELEC HD 21.5 S3
CONDUCTOR	:	Class 5 according to IEC 60228
INSULATION	:	PVC T11
INSULATION COLOR	:	HD 308
SHEATH	:	PVC T11
OPERATING TEMPERATURE	:	-50 70 °C
NOMINAL VOLTAGE	:	300/300V
TEST VOLTAGE	:	2 kV

To whom it may concern;

This is to certify that the following technical values are true and comply with the HAR standards

DIAMETERS

No. of Cores and Mm ² per conductor	NUMBER OF WIRES/ DIAMETER OF EACH WIRE (mm)	Insulation thickness Nominal mm	Outer diameter in Mm (0,1mm)	Max. resistance at 20°C (Ω/km)
2X0,50	15x0,20±0,004	0,50	3,00x4,90- 3,70x5,90	39,00
2x0,75	22x0,20±0,004	0,50	3,20x5,20- 3,80x6,30	26,00