

TAPD614BS LF14 - Break Stem Open

General Part Information		
Product Description		TAPD614BS LF14
Article Number		22052.00
Rivet Type	i	Break Stem Open
Standard Bulk Pack Quantity		3000.00
Application / Features	i	



Geometry / Dimensions / Performance		
Head Style	i	Large Flange
Body Diameter Ø (mm)		4.80
Body Length (mm)		16.50
Min. Grip Range (mm)		9.50
Max. Grip Range (mm)		11.10
Min. Hole Diameter (mm)		4.90
Max. Hole Diameter (mm)		5.00
Min. Flange Diameter (mm)		13.70
Max. Flange Diameter (mm)		14.30
Flange Thickness (mm)		2.00
Mandrel Diameter (mm)		2.64
Nominal Shear Strength (N)		2020.00
Nominal Tensile Strength (N)		2800.00

Material / Finish / Weight		
Body Material	i	AlMg3.5
Mandrel Material		Steel
Finish		Clean
Weight per thousand (kg)		3.40