

LED LENSER® M7RX – Rechargeable

This enormously powerful professional LED hand torch has an intelligent re-charge capability, energy management system and eight micro-controlled light options for maximum user control. Its awesome light intensity comes from a wide-angle reflector lens containing a state-of-the-art CREE Xtreme LED, blasting a maximum 600 lumens brightness up to 235 metres. It features the patented Advanced Focus System for quick, easy phasing from homogeneous, circular local light to a sharply, concentrated long-range beam, and has a one-handed Speed Focus for easy transition from flood to spot. Inside the torch a Smart Light Technology (SLT) suite includes two Energy Modes to regulate power usage, and eight Light Options - Power; Low Power; Blink; Boost; Dim; Defence Strobe; Morse and SOS - across three pre-set Light Programmes. Another helpful electronic feature is the Low Battery indicator, which indicates when batteries are running low. When that happens there's no need to replace batteries – LED Lenser's Floating Charge System conveniently allows the battery to be charged without even having to remove it from the housing. Once charged the M7RX is immediately ready for action. Its German-engineered, aircraft-grade aluminium body and gold-plated battery contacts make it a tough, dependable performer in the harshest environments but it is still reassuring to know that its modular construction allows for easy upgrade and replacement of components when required. Supplied in a protective hard storage case with rechargeable battery, mains charger, USB cable, wall-mount, wrist strap and 360° belt clip.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability second to none.

- Rechargeable medium sized torch packed full of the latest illumination technology
- Energy efficient CREE Xtreme LED Light Chip
- Increased light output from wide-angle, calibrated reflector lens
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology™. Micro-chip controlled multi-option technology with two energy usage modes, three pre-set light programs utilising eight light options (Morse, Dim, Boost, Power, Low Power, Blink, SOS, Defence Strobe)
- Floating Charge System™ – effortless contact recharging
- Dynamic Switch™ - Reactive, single switch control
- Speed Focus™ enables smooth single-handed beam focusing
- Fast Lock™ - locks the beam position and prevents accidental refocusing.
- 360° Belt Clip enables hands-free directional illumination
- Low Battery indicator
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant (IPX54)

Technical Information

Size: 156 x 37mm Ø

Power: 600 lumens max

Run Time: up to 8.5 hours

Beam Distance: up to 235m

Weight: 203grams

Supplied with : Hard Case, Mains Charger, USB cable, Wall Mount, Wrist-strap, 360° Belt Clip and Rechargeable Battery (1xLi-ion 3.7v)

Code	Colour	Packaging	Barcode
8307RX	Black	Hard Case	4029113830782