



Features

- 2 RS232 Serial Ports
- COM1 - COM8
- Interrupts 2-7,10-12, 14-15
- Line Drivers - 1 Mbit
- 64 byte fifo on each port

Specifications

- Ports: 2 x RS232
- Baud rates: Up to 921,600
- Data Bits: 5, 6, 7 or 8
- Stop bits: 1 or 2
- Parity: o,e,n,m or s
- Power: 425mA @ 5V
- Weight: 0.12kg
- Size: 13cm x 8.5cm

Applications

- RAS Server
- UPS Control
- Instrument Control
- Point of SaleHigh speed
- ISDN modems

ISA

2 Port Velocity RS232

Description



This is simply the highest performance 100% PC UART compatible RS232 card available today! The half size card provides two independent RS232 ports.

The UART clock can be set through software to provide maximum baud rates of either 921,600 baud, 460,800 baud, 230,400 baud, or 115,200 baud (standard PC).

Software

Serial Solutions Device Driver CD contains software for Windows 98, Windows 95, Windows NT4, Windows 3.x, DOS and OS/2.

Informative manuals and sample programs are supplied with full source code on CD!



ORDER

Description
ISA 2PORT VELOCITY RS232

Code
CC-124