



JUNCTION BOX

Abox GT 060-6²

Abox GT 060-6²

Junction box

CUSTOMIZABLE

110 x 110 x 67 mm
Article number: 49240601

Junction box - Industrial Quality - with connecting terminals for encapsulating acc. DIN EN 60670 and DIN EN 60529, weather-resistant and shockproof, for the assembly in flooded areas and in the ground without traffic loads, U_i=690V, with double-membrane seals M25, seal range 9 - 16 mm, with cast resin bag 600 ml (marking-free), funnel, ventilation seals and disposable gloves, Attention: Note the expiration date of the cast resin bag

Grey, with high-set screw terminal, 5-pole - 6 mm² (4 x 2.5² / 4 x 4² / 3 x 6²)



Technical data

Measures

Width:	110 mm
Length:	110 mm
Height:	67 mm

Material

Base:	polycarbonate, glass fiber-reinforced
Cover:	polycarbonate, glass fiber-reinforced

Accessory

BST M20 - Ventilation seal

DMS M20 - Double-membrane seals

DMS M25 - Double-membrane seals

GHB 3 - Cast-resin bag

KVR M20-GDB/MGM - Cable gland

KVR M20-MGM - Cable gland

VST M20 - Sealing plugs

VST M25 - Sealing plugs



JUNCTION BOX

Abox GT 060-6²

Other attributes

Entries:	9
Rated cross section:	6 mm ²
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Equipment:	Terminal
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP68 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	Yes