

HD 25/HD 25 SP

The Legend for
ENG and studio
Monitoring

The closed HD 25s are purpose-designed, closed dynamic, professional headphones for monitoring, recording and outdoor applications.

The closed, dynamic HD 25 SPs are the ideal headphones for DJ use in high noise environments.



HD 25



HD 25 SP

HD 25

- High sensitivity due to lightweight aluminium voice coils
- Capable of handling very high sound pressure levels
- Very lightweight and comfortable, even if used for long periods
- Rotatable capsule for one-ear listening
- Delivery includes: HD 25 Headphones
1 pair of soft earpads
pouch
Screw-on jack adapter, 3.5 mm to 6.3 mm

HD 25 SP

- Very lightweight and comfortable, even if used for long periods
- High maximum sound pressure level
- 60 Ω nominal impedance for universal capability
- Detachable cable
- High sensitivity due to lightweight aluminium/copper coils
- Delivery includes: HD 25 SP II Headphones
Screw-on jack adapter, 3.5 mm to 6.3 mm



Specifications

Headphones	HD 25
Transducer principle	dynamic, closed
Ear coupling	supra-aural
Frequency response (headphones)	16 – 22,000 Hz (- 3 dB)
Nominal impedance	70 Ω (HD 25-1 II) 70 Ω (HD 25-C II) 600 Ω (HD 25-13 II) 70 Ω (HD 25-II)
Load rating	0.2 W
Contact pressure	approx. 2.5 N
Sound pressure level (SPL)	120 dB (SPL)
THD, total harmonic distortion	< 0.3 %
Jack plug	3.5/6.3 mm stereo
Cable length	HD 25-1 II: 1,5 m HD 25-C II: 3 m (1 m) HD 25-13 II: 3 m HD 25-II: 2 m
Weight (without cable)	approx. 140 g



Headphones	HD 25 SP
Transducer principle	dynamic, closed
Ear coupling	supra-aural
Frequency response (headphones)	30 – 16,000 Hz (- 3 dB)
Nominal impedance	60 Ω
Characteristic SPL	100 dB ± 2 dB
Load rating	0.2 W
Contact pressure	approx. 3 N
THD, total harmonic distortion	< 0.4 %
Jack plug	3.5/6.3 mm stereo
Cable length	3 m
Weight (without cable)	115 g



Variants	Cat. No.	EAN	UPC
HD 25-II, detachable steel cable, 2 m	502105	40 44156 02099 0	6 15104 13214 6
HD 25-1 II, detachable steel cable, 1,5 m, right-angled	502188	40 44156 02379 3	6 15104 13570 3
HD 25-C II, detachable coiled cable, 3 m (1 m)	502104	40 44156 02098 3	6 15104 13213 9
HD 25-13 II, detachable steel cable, 3 m, 600 Ω	502102	40 44156 02096 9	6 15104 13211 5
HD 25 SP II, detachable cable, 3 m	502103	40 44156 02097 6	6 15104 13212 2