


## ZB4BL435

round head for pushbutton Ø 22 - spring return  
- projecting - red - OFF



### Main

Range of product	Harmony XB4
Product or component type	Head for pushbutton
Device short name	ZB4
Bezel material	Chromium plated metal
Mounting diameter	22 mm
Sale per indivisible quantity	1
IP degree of protection	IP66 IEC 60529
Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Projecting red OFF white

### Complementary

Resistance to high pressure washer	7000000 Pa 55 °C 0.1 m
Mechanical durability	5000000 cycles

### Environment

Protective treatment	TH
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Class of protection against electric shock	Class I IEC 60536
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK03 IEC 50102
Standards	CSA C22-2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508
Product certifications	BV CSA DNV (Det Norske Veritas) GL LROS (Lloyds register of shipping) RINA UL listed
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6
Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27 50 gn 11 ms half sine wave acceleration IEC 60068-2-27
RoHS EUR conformity date	0727
RoHS EUR status	Compliant