



8910DP12V14

Definite Purpose Contactor Type DP 20A, 2-Pole, 24VAC@50/60Hz



[Download your 8910DP12V14 datasheet](#)



[Characteristics](#) | Documents & Downloads

Main Hide

Product or component type	Definite Purpose Contactor
[In] rated current	20 A
Motor power hp	1 hp 115 V AC 1 phase 2 hp 230 V AC 1 phase
Poles description	2P
Pole contact composition	2 NO
Control circuit voltage	24 V AC 50/60 Hz

Complementary Hide

Product certifications	CE CSA UL listed
Locked rotor rated current	100 A 460 V AC 80 A 575 V AC 100 A 277 V AC
[Ue] rated operational voltage	600 V AC
Network number of phases	1 phase
Electrical connection	Quick connect terminals
Range of product	DP

Offer Sustainability Hide

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

Contractual warranty Hide

Period	18 months
---------------	-----------