


NI5002

IIA2010-N/1D/1G

Inductive sensors



Product characteristics

Inductive sensor
Metal thread M30 x 1.5
Cable
ATEX approval
Group II, category 1D
Group II, category 2G
Sensing range 10 mm; [f] flush mountable

Electrical data

Electrical design	Connection to certified intrinsically safe circuits with the max. values U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage [V]	8.2 DC; (1kΩ)
Supply voltage [V]	7.5...30 DC; when used outside the hazardous area
Current consumption [mA]	< 1 disabled; (> 2.1 mA enabled)
Protection class	III

Outputs

Output function	Normally closed
Current rating [mA]	< 30; when used outside the hazardous area
Switching frequency [Hz]	450

Range

Sensing range [mm]	10
Real sensing range (Sr) [mm]	10 ± 10 %

Accuracy / deviations

Correction factors	mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Environment

Ambient temperature [°C]	-20...80, when used outside hazardous areas
Protection	IP 67

Tests / approvals

Approval	PTB 01 ATEX 2191 BVS 04 ATEX E153 IECEX BVS 06.0003 TIIS TC16109
Marking of the unit	Ⓔ II 1G Ex ia IIB T6 Ga Ⓔ II 2G Ex ia IIC T6 Gb Ⓔ II 1D Ex ia IIIC T 90°C Da
EMC	EN 60947-5-6

NI5002

IIA2010-N/1D/1G

Inductive sensors

Shock / vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)
------------------------------	--------------------------------

MTTF [Years]	4963
--------------	------

Safety classification

Internal capacitance [nF]	< 145
---------------------------	-------

Internal inductance [μH]	< 140
--------------------------	-------

Mechanical data

Mounting	flush mountable
----------	-----------------

Housing materials	Brass special coating; active face: PBT
-------------------	-----------------------------------------

Weight [kg]	0.241
-------------	-------

Electrical connection


Connection	PVC cable / 2 m; 2 x 0.5 mm ²
------------	------------------------------------------

Wiring

Core colours

BN brown

BU blue



Accessories

Accessories (included)	2 lock nuts
------------------------	-------------

Remarks

Pack quantity [piece]	1
-----------------------	---