



ACCURATUS®
BY CERATECH

ACCURATUS 104M

USB Professional Magnetic Swipe Keyboard



Model Number: KYB500-104MUSBBK

Specification:

- With 104 Cherry MX keys based on Gold Crosspoint technology, and have tactile feeling
- Two different key actions (soft contact and keyclick)
- Laser-engraved keycap symbols or high quality UV silk screen printed keycap symbols
- Operating life cycle of individual keys :
 - Soft contact mode: 50 million strokes
 - Key click mode: 20 million strokes
- Damaged keys can be easily replaced and hence save the replacement cost
- With internal metal plate for key fixation, the protection against ESD is increased
- Can be upgraded to programmable version
- USB

Magnetic Swipe Reader Features:

- Comply with ISO 7812, IBM standards, American Driving License
- Support multi-country code settings
- Support programmable MSR setting for the header, tailor, separator, suffix and prefix, track sequence
- Track 1: 210BPI with max 76 characters
- Track 2: 210BPI with max 107 characters or 75BPI with max 37 characters
- Track 3: 210BPI with max 107 characters
- Card swipe speed: 10 to 100 cm/s
- 500,000 swipe cycles
- Available Configuration :
 - Dual Track: Track 1 & 2 or Track 2 & 3n
 - Three Track: Track 1, 2 & 3



Dimensions:

470(L) x 190(W) x 45(H) mm