






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
DS			□	RELEASED ECN<FC00-0016-99>	05/FEB/'99	JW CS
		A		REVISED ECN<FC00-0067-02>	30/APR/'02	JW CS
		B		REVISED ECN<FC00-0150-02>	21/DEC/'02	JW CS
		C		REVISED <ECR-07-015887>	13/DEC/'07	DR JK




SECTION A-A



- NOTE.
1. APPLICABLE ASS'Y CONNECTOR FOR
① JPT&MQS 81Pos.; P/N:368290-1
- ② TE TREAD MARK
③ CAVITY MARK
④ RECYCLE MARKING

©	YELLOW	PA66-GF15	RETAINER HSG<CHINA ONLY>	3 6 8 2 9 7- 1
	YELLOW	PA66-GF15	RETAINER HSG	3 6 8 2 9 7- 1
	COLOR	MATERIAL	DESCRIPTION	PART NO

THIS DRAWING IS CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWNDR G00		 Tyco Electronics AMP KOREA. kyungsan, korea			
		CHK YM CHOI					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
 3rd ANGLE PROJECTION		APVD JK SONG					
		0 <XX<10 ± 0.2 10<XX<30 ± 0.25 30<XX ± 0.3 ANGLES ± 3°		PRODUCT SPEC ---			
MATERIAL SEE TABLE		FINISH SEE TABLE		RETAINER HOUSING FOR MQS 76Pos.			
				APPLICATION SPEC ---			
		WEIGHT ---		SIZE	CAGE CODE	DRAWING NO	
				A3	00779	C- 3 6 8 2 9 7	
						SCALE 1/1	SHEET 1 OF 1