



CF-32GB

Introduction:

High capacity and high performance datastorage and communication media.
This memory card is designed for wide range of applications. Compatible devices include cell-phone, MP3 players, MP4 players, digital cameras, smartphone, tablet, GPS, Electronic books,
Excellent to capture RAW+JPEG and high definition video.
This card can be used also with motherboard to store data programs and card can be used for any other applications.

Features:

- Capacity : 32 Gbits
- Speed class : X600
- Read speed : 85 Mb/s
- Write speed : 45 Mb/s
- Design for professional DSLR
- Support UDMA Mode 6
- Extreme speed fast UDMA raw.
- Supply voltage : 3,3V / 5,0V
- Operating current at 5,0V : 0,2mA (Sleep mode), 15mA (Stand by mode), 65mA (Operating mode).
- Operating current at 3,3V : 0,2mA (Sleep mode), 8mA (Stand by mode), 40mA (Operating mode).
- Durability : 10.000 insertion/removal cycles.
- Operating temperature : 0°C at +70°C.
- Storage temperature : -40°C at +85°C.
- Dimensions : 42,8 x 36,4 x 3,3mm

Others products:

CF-512MB

CF-1GB

CF-16GB

CF-32GB

CF-64GB

CF-128GB



Item includes:

C-F card in a packaging.
Technical datasheet available in English.

Products informations : www.seeit.fr

Distributors : www.rs-components.com