



Datasheet

RS PRO Medium Duty Swivel braked Castor

Stock number: 687326

EN



Medium duty castor with bright zinc finish.
Press steel bracket with ball bearing swivel head.
Black nylon centre with blue rubber tyre.

Wheel diameter:	75mm
Thread width:	32mm
Load Capacity:	90kg
Overall height:	95mm
Plate size:	105mm x 80mm
Bolt hole centres:	80/86mm x 60mm
Suits bolt diameter:	8mm
Rotation:	Swivel
Brake:	Yes
Wheel type:	Hub black nylon, with blue rubber tyre
Bearing type:	Plain
Swivel radius:	62mm

