



Datasheet MOBILE STEP-A-TRUCKS

ENGLISH

With 2 or 3 treads

RS Stock No. 789-8494

RS Stock No. 789-8497



Comply to EN-131 standard.

Versatile – neat & compact.

Large toe plate & wide step treads.

Load Capacity: as Sack Truck – 60kg, as Step Unit – 150 kg.

Multi purpose units, simple & easy to convert from steps to sack trucks.

When in sack truck mode they are mobile on two 100mm wheels.

| Size when folded W x D x H mm | Size as Sack truck W x D x H mm | Size as Step unit W x D x H mm | Sack Truck Toe Plate mm | Step Tread Size mm | No. of Treads | Weight kg | Model |
|----------------------------------|------------------------------------|-----------------------------------|-------------------------------|--------------------------|------------------|--------------|--------|
| 460 x 70 x 990 | 480 x 490 x 990 | 470 x 530 x 920 | 390 x 280 | 375 x 210 | 2 | 6.5 | FMS82Y |
| 470 x 90 x 1265 | 490 x 450 x 1265 | 470 x 735 x 1190 | | | 3 | 9 | FMS83Y |