



Sample photo

Order symbol: ALN 161609
Product nbr: 7811270
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016126
El. number:
 Finland:
 :

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		163	162	91	Ingress Protection (EN 60529): IP 66/67/68
inch:		6.4	6.4	3.6	Impact Resistance (EN 62262): IK 08
Materials:					NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:	Aluminium				Certificates: Underwriters Laboratories Fimko UL Canada Gost R
Base colour:	RAL 7001				
Cover colour:	RAL 7001				
Cover screws material:	Stainless steel				
Gasket material:	Polyurethane				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
AM 1616	Mounting plate				
ARM 0615	DIN-15 Mounting rail				
ARH 16	DIN-35 Mounting rail				
MR 75005	Selftapping taptite screw M5				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

