




NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION
- 2

 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 50 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
INDIVIDUALLY PACKED ASSEMBLY
- 4

 DAT LABEL INFO:
 - UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.
- 5

 BLANK LABEL

- 6 CABLE INFO:
- CORE DIA

OUTER DIA

JACKET COLOR

JACKET MATERIAL
- 50/125 μ m

— 2,5 x 5,0 mm

— ORANGE

— LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349561-Y	XY,0
4-5349561-1	1,5
9-5349561-1	15,5

2	—	DAT-85 LABEL	7
4	—	PROTECTIVE COVER, 2.5MM, BLACK	6
4	—	KIT, MM, CER, ASSY, BULK	5
4	—	CRIMP EYELET, BRIGHT TIN	4
2	—	FOAC BOOT 2.5BAY,BLACK	3
2	—	FOAC BOOT 2.5BAY,RED	2
L	—	FOCAB 2.5 50/125 DUPLEX ORANGE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

$\pm$

$\pm$

$\pm$

$\pm$

$\pm$

$\pm$

—

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

13 SEP 05

13 SEP 05

13 SEP 05

—

—

—

—

tyco
Electronics

Tyco Electronics Corporation
FOBU, Bangalore, India

NAME

FOMM50 LEAD 2,5mm TZ ST - ST DPX

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=5349561

—

SCALE

NTS

SHEET

1

OF

1

REV

A