



Verbatim LED Classic A E27 8W 2700K Warm White 530 LM DIM


- E27 Socket
- 220 - 240 Voltage
- 30,000 hours Lifetime
- Dimmable
- 82% Energy Saving
- Lumen: 530
- Equivalent to 43W incandescent bulb

Product Number	52148
General Data	
Lamp Socket	E27
Electric Data	
Wattage (W)	8
Wattage Equivalent (W)	43
Voltage (V)	220 - 240
Dimmable	yes
Power Factor	0.85
Operating Frequency (Hz)	50-60
Geometric Data	
Length (mm)	112
Diameter (in mm)	60
Weight (g)	175
Photometric Data	
Luminous Flux (lm)	530
CRI	≥ 80
CCT (K)	2700
Beam Angle (°)	130
Luminous Efficacy (lm/W)	66.3
Lifetime (hrs)	30,000
Switching Cycle	20,000



02/07/2014


Photometric Diagrams



Distance [m]	Cone Diameter [m]	Illuminance [lx]	E(0°)	E(C90)	E(C0)
0.5	2.73 2.38	553 11 16	69.9°	67.2°	
1.0	5.47 4.76	138 3 4	69.9°	67.2°	
1.5	8.20 7.14	61 1 2	69.9°	67.2°	
2.0	10.93 9.52	35 1 1	69.9°	67.2°	
2.5	13.66 11.89	22 0 1	69.9°	67.2°	
3.0	16.40 14.27	15 0 0	69.9°	67.2°	

Distance [m] Cone Diameter [m] Illuminance [lx]
 — C0 - C180 (Half-value Angle: 134.4°)
 — C90 - C270 (Half-value Angle: 139.8°)

Energy Rating



Technical Packaging Details

Barcode

023942521488

EAN 128

(02)00023942521488(37)04(91)204

EAN 14

50023942521483

Pack Dimensions(HxWxL)

178 x 118 x 61

Pack Weight

201

MOQ

4

Carton Dimensions (HxWxL)

195 x 144 x 253

Cartons/Pallet

80

Layers/Pallet

4

Units/Pallet

320

02/07/2014