

Circuit breakers for power distribution

A2 Ordering information



A2 250A - Fixed (F) 1 pole - Front terminals (F)
Thermomagnetic trip unit - TMF Icu (240 V)

In	I ₃	A (10kA)	N (14kA)
125	1250	A2A125TW-1	A2N125TW-1
150	1500	A2A150TW-1	A2N150TW-1
175	1750	A2A175TW-1	A2N175TW-1
200	2000	A2A200TW-1	A2N200TW-1
225	2250	A2A225TW-1	A2N225TW-1
250	2500	A2A250TW-1	A2N250TW-1



A2 250A - Fixed (F) 2 pole - Front terminals (F)
Thermomagnetic trip unit - TMF Icu (240 V)

In	I ₃	A (10kA)	N (25kA)
125	1250	A2A125TW-2	A2N125TW-2
150	1500	A2A150TW-2	A2N150TW-2
175	1750	A2A175TW-2	A2N175TW-2
200	2000	A2A200TW-2	A2N200TW-2
225	2250	A2A225TW-2	A2N225TW-2
250	2500	A2A250TW-2	A2N250TW-2



A2 250A - Fixed (F) 3 pole - Front terminals (F)
Thermomagnetic trip unit - TMF Icu (240 V)

In	I ₃	A (10kA)	N (25kA)
125	1250	A2A125TW	A2N125TW
150	1500	A2A150TW	A2N150TW
175	1750	A2A175TW	A2N175TW
200	2000	A2A200TW	A2N200TW
225	2250	A2A225TW	A2N225TW
250	2500	A2A250TW	A2N250TW