PRODUCT DATASHEET
Strada-T series

last update 27/6/2013



Ordering number	**CA12332**
Description	**1**

Family	Strada-T	FWHM	(simulated) Asym
Type	Assembly	Efficiency	(simulated) 90 %
LED	6J (GTDW16)	cd/lm	(simulated) 0.000
Color	Clear	Gerber File	Available
Diameter	19.6 x 15.5 mm		
Height	9.6 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	On production		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

Ledil Oy
Salorankatu 10
24240 SALO
Finland

http://www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001



Isometric view



Bottom view



Beam direction



Front view



Strada lens arrangement recomendation



Top view

MATERIALS
Lens: PMMA
Tape(optional): PU Foam

Part no. with tape fastening: CA12332_Strada-T-DN

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.

Ledil Oy
Salorankatu 10
FIN-24100 SALO
Finland

DRAWN BY: ah	DATE: 13.12.2011	DRAWING TITLE: Datasheet Strada-T-DN Lens			
CHECKED BY: vs	DATE: 13.12.2011	SIZE: A4	DRAWING NUMBER: C12329		REV: 1
DESIGNED BY: hh	DATE: 07.09.2011	SCALE: 2:1	WEIGHT(g):		SHEET: 1/1