

Datasheet

RS Pro 12 W LED Strip Light, T4, 230 V ac, Cool White, 7500K

RS Stock No: **720-3827**



Product Details

RS Pro 12 W LED strip light delivers colour temperature up to 7500K. The cool white light has a voltage rating of 230 V ac. This ultra-slim, low profile, linkable, low power LED strip lighting forms a direct replacement for your existing T4 fluorescent lighting. This light offers brilliant protection by using internal fuse.

Features and Benefits

- Low power consumption
- Up to 10 years continuous operation
- Cool running
- Integral on/off switch
- Internal fuse protection
- Easily "daisy chained" together using link cables

**Specifications:**

Colour Temperature	7500 K
Depth	44 mm
Diffuser Finish	Clear
Dimensions	620 x 20 x 44 mm
Dimmable	No
EU Energy Efficiency Rating	A++
Finish	White
Lamp Base	T4
Lamp Supplied	Yes
Lamp Type	LED
Length	620 mm
Light Colour	Cool White
Type	Strip Light
Voltage Rating	230 V ac
Wattage	12 W
Width	20 mm