

# Sealing frame - CES-B16-HFFS-PLBK - 0801662

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Sealing frame with locking latch, size B16, with flat gasket, for 8 small sleeves



## Key commercial data

Packing unit	1 pc
GTIN	 4 046356 674102
Weight per Piece (excluding packing)	145.3 g
Custom tariff number	85472000
Country of origin	Poland

## Technical data

### Dimensions

Length	120 mm
Width	58.5 mm
Height	20 mm

### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 120 °C

### General

Frame type	Sealing frame
Material	PA
Inflammability class according to UL 94	V0
Color	black
Installation instructions	One large sleeve requires the space of 4 small sleeves, M4 mounting screws
	Leak-tightness is guaranteed with underwall and perpendicular mounting; the CES-B24-WRG-BK flat gasket (supplied as standard)

# Sealing frame - CES-B16-HFFS-PLBK - 0801662

## Technical data

### General

	should be inserted between the wall and the sealing frame in the case of wall mounting.
--	---

## Classifications

### eCl@ss

eCl@ss 4.0	23110102
eCl@ss 4.1	23110102
eCl@ss 5.0	23110102
eCl@ss 5.1	23110102
eCl@ss 6.0	23110102
eCl@ss 7.0	23110102
eCl@ss 8.0	23110102

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC002498

### UNSPSC

UNSPSC 6.01	27113201
UNSPSC 7.0901	27113201
UNSPSC 11	27113201
UNSPSC 12.01	27113201
UNSPSC 13.2	27113201

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

# Sealing frame - CES-B16-HFFS-PLBK - 0801662

## Approvals

UL Recognized

cUL Recognized

cULus Recognized

## Accessories

Accessories

Seal


Flat gasket - CES-B16-WRG-BK - 0801726



Flat gasket made of NBR, size B16


## Drawings

Dimensioned drawing



Dimensional drawing

Dimensioned drawing



Panel cutout