







THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD. DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.

3-1734282-X	37-37	69.34	63.50	55.42	54.80	49.86
2-1734282-X	25-25	53.10	47.04	38.96	38.30	33.24
1-1734282-X	15-15	39.30	33.30	25.25	24.60	19.39
1734282-X	9-9	30.95	24.99	16.92	16.20	11.08
PART NO.	PINS	A	B	C	D	E



X-1734282-6	30 u"	PC99/ACTUAL COLOR	37-37 NOT AVAILABLE
X-1734282-5	10 u"	PC99/ACTUAL COLOR	
X-1734282-4	GOLD FLASH	PC99/ACTUAL COLOR	
X-1734282-3	30 u"	BLACK	
X-1734282-2	10 u"	BLACK	
X-1734282-1	GOLD FLASH	BLACK	
PART NO.	GOLD PLATING	HSG COLOR	


0	NEW RELEASE	--	JL	SH	30JUN 2005
LTR	REVISION RECORD	ECN	DWN	CHK	DATE



NOTES:


- MATERIAL:
 - HOUSING/BACK COVER: THERMOPLASTIC, UL94V-0; COLOR: SEE TABLE.
 - CONTACTS: COPPER ALLOY
 - BOARDLOCK: COPPER ALLOY
 - BRACKET: ZINC ALLOY
 - SHELL: STEEL
- FINISH:
 - CONTACT: GOLD PLATING (SEE TABLE) ON CONTACT AREA. 100μ" MIN. BRIGHT TIN PLATING ON SOLDER TAIL AREA, 50μ" MIN. NICKEL UNDERPLATING OVERALL.
 - BOARDLOCK: 60μ" MIN. TIN PLATING OVERALL.
 - SHELL: 60μ" MIN. TIN PLATING OVERALL.
- WAVE SOLDER CAPABLE TO 265°C PER TYCO SPEC. 109-202, CONDITION B.

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.2 3 PLC ± ANGLES ±3°	DWN	J. LEE 30-JUN-2005	tyco Electronics TYCO HOLDINGS (BERMUDA) VII LTD. TAIWAN BRANCH
	CHK	S. HOU 30-JUN-2005	
MATERIAL SEE NOTE	APVD	W.J. KE 30-JUN-2005	D-SUB STACKED PLUG OVER RCPT, R/A TYPE, THREAD INSERTS
	PRODUCT SPEC	108-57517	
FINISH SEE NOTE	QUALIFICATION TEST REPORT	501-57590	LOC DW
	WEIGHT		SCALE --
		SHEET 1 OF 2	REV O



CARTON

LABEL




TOP COVER

TRAY

- NOTE :
- 1. DIMENSION :
TRAY : L=310, W=215, H=30
CARTON : L=335, W=230, H=280
 - 2. TRAY : PS or PET
 - 3. QUANTITY:

PIN NO.	9-9	15-15	25-25	37-37
PCS/TRAY	36	28	20	16
TRAY/CARTON	10	10	10	10
PCS/CARTON	360	280	200	160
NET WT.(KG/CARTON)	9.72	9.62	9.38	10.3
GROSS WT.(KG/CARTON)	11.22	11.05	10.81	11.46



TRAY LAYOUT

	SEE SHEET 1			
LTR	REVISION RECORD	ECN	DWN CHK	DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.2 3 PLC ± ANGLES ±3°		DWN	J. LEE 30-JUN-2005	tyco TYCO HOLDINGS (BERMUDA) Electronics VII LTD. TAIWAN BRANCH	
		CHK	S. HOU 30-JUN-2005		
MATERIAL SEE NOTE		APVD	W.J. KE 30-JUN-2005	NAME D-SUB STACKED PLUG OVER RCPT, R/A TYPE, THREAD INSERTS	
		PRODUCT SPEC	-		
FINISH SEE NOTE		QUALIFICATION TEST REPORT	-	LOC	SIZE
		WEIGHT	-	DW	A ₃
		DRAWING NO C-1734282		REV	O
		SCALE --		SHEET 2 OF 2	