



**Label mount, blank**

**Part no. M22-XCK**

**Article no. 279433**



Powering Business Worldwide™

4 positions, use M22-A4 fixing adaptor

### Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Single unit/Complete unit			Single unit
Name			No inscription
For use with			Joystick 4-way selector switch actuators
Connection to SmartWire-DT			no

### General

Standards			IEC/EN 60947 VDE 0660
Climatic proofing			Damp heat, constant to IEC 60068-2-78 Damp heat, cyclic to IEC 60068-2-30
Ambient temperature		°C	
Open		°C	- 25 - + 70
Mounting position			As required

### Technical data ETIM 4.0

Height			60
External diameter		mm	0
Width		mm	60
ISO symbol inscription			-
Form			quadratic
Inscription			-
Color			Silver

### Additional product information (links)

<b>IL04716002Z (AWA1160-1745) RMQ-Titan System</b>	
IL04716002Z (AWA1160-1745) RMQ-Titan System	<a href="ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2011_03.pdf">ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2011_03.pdf</a>
Labeleditor	<a href="ftp://ftp.moeller.net/MFD/EASY-SOFT-PRO/labeleditor_206.exe">ftp://ftp.moeller.net/MFD/EASY-SOFT-PRO/labeleditor_206.exe</a>